

Outdoor Unibody Cabinet

Data Solutions



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity.

CERTIFICATIONS



FEATURES

Double-walled, Al

IP 55

One-piece inner case with removable outer cladding

Heat dissipation through natural convection, max. 5 W/K (11249-003) / 6 W/K (11249-005)

SPECIFICATIONS

Material: Алюминий

Table 1/3

Catalog Number	Product Type	Product Family	Rack Height	Высота мм	Ширина мм	Глубина мм
11249-005	Outdoor Cabinet	Unibody	20U	1100mm	700mm	500mm

CatalogNumber	Product Type	Product Family	Rack Height	Высота мм	Ширина мм	Глубина мм
11249-003	Outdoor Cabinet	Unibody	16U	930mm	700mm	500mm

Table 2/3

Catalog Number	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
11249-005	Double Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
11249-003	Double Walled	Single Door	С передней стороны	Natural Convection	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Table 3/3

Catalog Number	Package Quantity	Finish
11249-005	1	Powder Coated
11249-003	1	Powder Coated

ADDITIONAL PRODUCT DETAILS

Please order panel/slide mounts separately.

Further base/plinth heights on request.

Please order wall-mounting assembly kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE