


Запирающая панель для разделения воздуха Varistar CP, ширина 800 мм, С выемками

Data Solutions



Присадочная панель для шкафов шириной 800 мм для предотвращения рециркуляции воздуха в стойках с охлаждением спереди назад. Гладкие панели и панели с вырезами для прокладки кабелей спереди и сзади со щеточными пыльниками и кабельными пальцами.

FEATURES

Изоляция воздушных потоков, заглушки для шкафов шириной 800 мм

Сетевые и серверные шкафы могут быть смонтированы в ряд

Уплотнители, UL 94 HF-1, -20 °C ... 100° C

Сплошные панели

Заглушки предотвращают нежелательное замыкание воздушных линий, т. е. смешивание горячего отработанного воздуха с холодным приточным

Only compatible with heavy load crossbar, not compatible with reduction brackets

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Material: Сталь

Table 1/2

Catalog Number	Rack Height	Высота мм	Package Quantity	Color	Color Code	Finish
21630-147	42U	2000mm	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Rack Height	Высота мм	Package Quantity	Color	Color Code	Finish
21630-149	52U	2450mm	1	Black Grey	RAL 7021	Powder Coated
21630-148	47U	2200mm	1	Black Grey	RAL 7021	Powder Coated

Table 2/2		
Catalog Number	Protection Rating	Type
21630-147	IP20	Cable Duct
21630-149	IP20	Cable Duct
21630-148	IP20	Cable Duct

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE