

Joint Bond T8 Mold Welder Frame Assembly, Power



FEATURES

Replacement welder frame assembly for T8 joint bond welders

Includes frame with mold lid, mold handle, mold cleaner and flint ignitor

SPECIFICATIONS

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: C

Table 1/1

Catalog Number	Material	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBCT8X6X	Graphite, Steel, Thermoplastic	120 mm ² Ropelay	9.53mm	T8
PBCT82W13X	Graphite, Steel, Thermoplastic	250 kcmil Ropelay	19.05mm	T8

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE