

nVent ERICO Railclips, Hammer-On, Conductor Parallel Inside



FEATURES

"Hammer-on" design

Securely holds conductors, reducing maintenance and improving wayside safety

Quick and easy hammer-on installation

Fits various rail profiles

Does not require removal of the ballast material

Multi-layer proprietary coating provides optimal corrosion protection

SPECIFICATIONS

Rail Type: 40 kg to 65 kg T-Rail Sections


Finish: Multi-Layer Proprietary Coating

Material: Spring Steel

Table 1/1

Catalog Number	Article Number	Длина мм (L)	Width (W)	Rail Foot Thickness (RFT)	Diameter (Ø)
EM58SN1SH	595340	34.04mm	44.45 mm	8 - 14 mm	9.5 - 11 mm
EM58C1214	595120	34.04mm	44.45 mm	8 - 14 mm	12 - 14 mm
EM58SN2SH	595290	34.04mm	44.45 mm	8 - 14 mm	13.5 - 155 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE