

Special Track Work Complete Welder, Power



FEATURES

Designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

SPECIFICATIONS

Rail Type: Crane Rail Profiles

Bond Terminal Style: J

Table 1/1

Catalog Number	Material	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation	Handle Length
PBJT503LH	Сталь, Graphite	2/0 Concentric	10.62mm	T5	Left Hand	502mm
PBJT52WLH	Сталь, Graphite	250 kcmil Ropelay	19.05mm	T5	Left Hand	502mm
PBJT52WRH	Graphite, Сталь	250 kcmil Ropelay	19.05mm	T5	Right Hand	502mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE