

DH Distance Holder and Spacer



CERTIFICATIONS



FEATURES

To make higher plates, screens or profiles

Male-female allowing stable mounting

Electrotechnical applications

SPECIFICATIONS

Insulation Voltage:	1000V
Finish:	Electrogalvanized
Flammability Rating:	UL® 94HB
Temperature:	80 °C Max

Table 1/2

Catalog Number	Article Number	Material	Thread Size (TS)	Thread Length (TL)	Thread Depth (TD)	Длина мм (L)
DH15M5	560660	Сталь, Polystyrene	M5	7mm	7mm	15mm
DH15M6	560740	Сталь, Polystyrene	M6	7mm	8mm	15mm


CatalogNumber	Article Number	Material	Thread Size (TS)	Thread Length (TL)	Thread Depth (TD)	Длина мм (L)
DH20M5	560670	Сталь, Polystyrene	M5	7mm	7mm	20mm
DH20M6	560750	Сталь, Polystyrene	M6	7mm	8mm	20mm
DH30M5	560600	Сталь, Polystyrene	M5	7mm	7mm	30mm
DH30M6	560700	Сталь, Polystyrene	M6	7mm	8mm	30mm
DH45M5	560610	Сталь, Polystyrene	M5	7mm	7mm	45mm
DH45M6	560710	Сталь, Polystyrene	M6	7mm	8mm	45mm
DH55M5	560620	Сталь, Polystyrene	M5	7mm	7mm	55mm
DH70M5	560630	Сталь, Polystyrene	M5	7mm	7mm	70mm
DH120M5	560650	Сталь, Polystyrene	M5	7mm	7mm	120mm
DH70M6	560720	Сталь, Polystyrene	M6	7mm	8mm	70mm
DH85M5	560640	Сталь, Polystyrene	M5	7mm	7mm	85mm
DH120M6	560730	Сталь, Polystyrene	M6	7mm	8mm	120mm

Table 2/2

Catalog Number	Article Number	Width (W)	Unit Weight
DH15M5	560660	13 mm	0 kg
DH15M6	560740	13 mm	0 kg
DH20M5	560670	13 mm	0.01 kg
DH20M6	560750	13 mm	0.01 kg
DH30M5	560600	13 mm	0.01 kg

Catalog Number	Article Number	Width (W)	Unit Weight
DH30M6	560700	13 mm	0.01 kg
DH45M5	560610	13 mm	0.01 kg
DH45M6	560710	13 mm	0.01 kg
DH55M5	560620	13 mm	0.01 kg
DH70M5	560630	13 mm	0.01 kg
DH120M5	560650	13 mm	0.02 kg
DH70M6	560720	13 mm	0.02 kg
DH85M5	560640	13 mm	0.02 kg
DH120M6	560730	13 mm	0.04 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE