

## , DHP



Mounting profiles are used to fit accessories to the door frame for easy and secure mounting of cables, ducts, etc.

### FEATURES

---

Description: Horizontal profiles with 25 mm hole pattern of 4.5 mm and 6.5 mm of diameter for the attachment and installation of equipment.

Material: 1.5 mm galvanized steel.

Pack quantity: 5 pieces with mounting accessories.

Mounting requirements: They fit directly onto the MMDP door mounting profiles. They can also be mounted vertically onto two horizontal profiles. For doors with espagnolette locking system, profiles must be cut where indicated.

SPECIFICATIONS

Thickness: 1.5mm  
Finish: Galvanized  
Material: Mild Steel

| Table 1/1      |           |           |            |                  |            |
|----------------|-----------|-----------|------------|------------------|------------|
| Catalog Number | Высота мм | Ширина мм | Глубина мм | Package Quantity | Quick Ship |
| DHP040         | 25mm      | 348mm     | 12mm       | 5                | No         |
| DHP050         | 25mm      | 448mm     | 12mm       | 5                | No         |
| DHP030         | 25mm      | 248mm     | 12mm       | 5                | No         |
| DHP060         | 25mm      | 548mm     | 12mm       | 5                | No         |
| DHP080         | 25mm      | 748mm     | 12mm       | 5                | No         |

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE