

, ESFC



A swing frame for 19" equipment that provides additional mounting space for such equipment, as well as rear access to the fitted components and equipment once opened.

FEATURES

Description: Full height swing frame for 19" components allowing left and right hand opening. Can be used in steel, combinable and compact enclosures. Hinges designed to give extra build-in depth. Adjustable top hinge for square mounting of the swing frame. Rigid W-shaped frame profile for heavy equipment. Zinc plated 19" vertical profiles for direct earthing of the mounted components. Standard equipped with 130° hinges. Can also be mounted on the side of 600 mm deep floor standing enclosures. For steel, combinable enclosures use transversal support bars ESFB in combination with VBD if required. Adjustable in depth by steps of 12.5 mm.

Maximum load: 1800N, supplied with a self positioning device.

Lock: Two 3 mm double-bit locks.

Material: 19" vertical profiles 2 mm zinc plated steel. Frame: vertical profiles 2 mm and horizontal profiles 3 mm.

Pack quantity: 1 swing frame with hinges.

Mounting requirements: ESFC for 600 mm, 800 mm, 1000 mm, 1200 mm wide steel, combinable enclosures. Add ESFB for mounting in a steel, combinable enclosure.

SPECIFICATIONS

Thickness: 2mm

Material:Mild SteelFinish:Zinc Plated

| Table 1/1 | | | | | | |
|----------------|-----------|-----------|------------|------------|-----------------------|------------|
| Catalog Number | Высота мм | Ширина мм | Глубина мм | Rack Units | Enclosure Material | Quick Ship |
| ESFC316 | 1600mm | 499mm | 80mm | 31U | Mild Steel | No |
| ESFC406 | 2000mm | 499mm | 80mm | 40U | Mild Steel | No |
| ESFC276 | 1400mm | 499mm | 80mm | 27U | Mild Steel | No |
| ESFC366 | 1800mm | 499mm | 80mm | 36U | Mild Steel | No |
| ESFC456 | 2200mm | 499mm | 80mm | 45U | Mild Steel | No |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE