

19", AVP



19" equipment can be easily fitted in wall mounted enclosures, either in the factory or in the field, when these profiles are used.

FEATURES

Description: For 600 mm wide enclosures only. Adjustable depth with the use of the AMG accessory. Usable depth between 19" profiles and external door: 56 mm. Fitted onto the hinge holes located on the front frame of the enclosure. For stainless steel enclosures, machining is required.

Material: 2 mm galvanized steel.

Pack quantity: 1 pair with mounting accessories.

SPECIFICATIONS

Thickness: 2mm
Finish: Galvanized
Material: Mild Steel

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Rack Units	Enclosure Material	Quick Ship
AVP0600	600mm	55mm	50mm	13U	Mild Steel	No
AVP1200	1200mm	55mm	50mm	26U	Mild Steel	No
AVP0800	800mm	55mm	50mm	17U	Mild Steel	No
AVP1000	1000mm	55mm	50mm	21U	Mild Steel	No

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE