

, CRG



The roof plate with gland plate openings allow for easy cable entry in the field. Standard alternative solutions are available, which means that gland plates best suited for the application at hand can be used.

FEATURES

Description: Roof plate with gland plates for cable entry.

Material: 1.5 mm steel plate.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece with gland plates, gaskets and mounting accessories.

Standard alternative solutions give customers the flexibility to use a gland plate that best suits the application, reducing labour time as machining is not required

The protection degree of the enclosure is maintained when the gland plate are mounted

Standard off the shelf wall mounted enclosure gland plates with different cabling options, are available as replacements

Roof plate with gland plates for cable entry

One piece with gland plates, gaskets and mounting accessories

SPECIFICATIONS

Thickness: 1.5mm
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Gland Plate Opening Width	Gland Plate Opening Depth	Number of Gland Plate Openings
CRG0808R5	17mm	800mm	800mm	210mm	96mm	2
CRG0806R5	17mm	800mm	600mm	210mm	96mm	2
CRG0608R5	17mm	600mm	800mm	310mm	96mm	1
CRG0606R5	17mm	600mm	600mm	310mm	96mm	1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE