

# 19-дюймовая передняя панель для кабельных наконечников

19-дюймовая передняя панель предназначена для размещения кабельных наконечников.



## CERTIFICATIONS



## FEATURES

19-дюймовая передняя панель для установки кабельных наконечников (монтаж кабельных наконечников,, ввод и вращение на 45°)

## SPECIFICATIONS

|                       |                 |
|-----------------------|-----------------|
| <b>Глубина мм:</b>    | 1.5mm           |
| <b>Rack Width:</b>    | 95HP            |
| <b>Аксессуар Тип:</b> | Передняя панель |
| <b>Product Type:</b>  | Передняя панель |
| <b>Material:</b>      | Сталь           |

Table 1/2

| Catalog Number | Rack Height | Mounting       | Package Quantity | Front Finish | Rear Finish | Color Code |
|----------------|-------------|----------------|------------------|--------------|-------------|------------|
| 20118-761      | 1U          | Screw-on Front | 1                | Painted      | Painted     | RAL 7035   |

| CatalogNumber | Rack Height | Mounting       | Package Quantity | Front Finish | Rear Finish | Color Code |
|---------------|-------------|----------------|------------------|--------------|-------------|------------|
| 20118-762     | 1U          | Screw-on Front | 1                | Painted      | Painted     | RAL 7021   |

Table 2/2

| Catalog Number | EMC Shielding | Finish        | Высота мм | Type            | Ширина мм | Quick Ship |
|----------------|---------------|---------------|-----------|-----------------|-----------|------------|
| 20118-761      | Нет           | Powder Coated | 43.6mm    | 19" Front Panel | 483mm     | No         |
| 20118-762      | Нет           | Powder Coated | 43.6mm    | 19" Front Panel | 483mm     | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**