

19-дюйм. нагнетательный вентилятор, 2 U, осевой

Лоток вентилятора со встроенным нагнетательным вентилятором.



CERTIFICATIONS



FEATURES

Защита от прикосновения в соответствии с DIN EN ISO 13857

Встроенный воздуховод предотвращает накопление тепла в расположенных ниже модулях

Возможность использования в комбинации с блочным каркасом

Возможна комплектация дополнительным вентилятором с задней стороны, 2 U, для активного охлаждения модулей под нагнетательным вентилятором

SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Quick Ship
10713-526	230V		1	Aluminum-Zinc Plated	Сталь, Polypropylene	No
10713-518	230V		1	Aluminum-Zinc Plated	Сталь, Polypropylene	No

CatalogNumber	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Quick Ship
10713-536	115V		1	Aluminum-Zinc Plated	Сталь, Polypropylene	No
10713-534	230V		1	Aluminum-Zinc Plated	Сталь, Polypropylene	No
19713-540			1	Aluminum-Zinc Plated	Сталь, Polypropylene	No
10713-520	115V		1	Aluminum-Zinc Plated	Сталь, Polypropylene	No
10713-537		24V min	1	Aluminum-Zinc Plated	Сталь, Polypropylene	No
10713-529		24V min	1	Aluminum-Zinc Plated	Сталь, Polypropylene	No

ADDITIONAL PRODUCT DETAILS

Сетевой кабель заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE