

Система АТСА, серия FC 450/40, 14 слотов, ПОСТОЯННЫЙ ТОК



Серия nVent SCHROFF ATCA 450/40 представляет собой линейку плат управления шасси AdvancedTCA, которые обеспечивают охлаждение и питание 450 Вт на слот для плат. The backplane is verified in accordance to 40GBASE-KR4 for 40 Gbit Ethernet. Доступны корпуса с воздушным потоком снизу вверх, а также корпуса с воздушным потоком спереди назад.

CERTIFICATIONS



FEATURES

Соответствует стандарту AdvancedTCA PICMG, 3,0 ред. 3.0

Входное напряжение -48 В пост. тока/-60 В пост. тока, два резервированных модуля питания (РЕМ)

2 резервированных вентиляторных блока с функцией горячей замены (приточно-вытяжное охлаждение)

Охлаждающая способность 450 Вт на слот при температуре окружающей среды 55 °C

Подготовлено для 2 плат управления шасси SCHROFF с Pigeon Point ShMM 700

Слоты для плат управления шасси справа в корзине для плат AdvancedTCA

Консоли плат управления шасси и интерфейс сигнализации Telco в нижнем вентиляторном модуле

Доступ к воздушным фильтрам спереди

SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Number of Slots	Type	Backplane Type	Data Transfer	Power per Slot
11990-192	System	14	19" Rack Mount	Dual Star, Bussed IPMB	40 GbE	450W

CatalogNumber	Product Type	Number ofSlots	Type	BackplaneType	Data Transfer	Power per Slot
11990-190	System	14	19" Rack Mount	Dual Star, Bussed IPMB	40 GbE	450W

Table 2/3

Catalog Number	Input Voltage DC	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O
11990-192	-48V, -60V	Front to Rear	14U	(2) DC PEM	Да	Да
11990-190	-48V, -60V	Bottom to Top	14U	(2) DC PEM	Да	Да

Table 3/3

Catalog Number	Complies With	Глубина мм	Package Quantity	Quick Ship
11990-192	PICMG 3.0 R3.0	383mm	1	No
11990-190	PICMG 3.0 R3.0	383mm	1	No

ADDITIONAL PRODUCT DETAILS

Модифицированные системы доступны по запросу.

Полностью собрано, подключено и протестировано.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE