


Передняя панель CompasPRO

Передняя панель для корпусов compasPRO крепится болтами к передней раме корпуса.



CERTIFICATIONS



FEATURES

Передняя панель крепится болтами к передней раме корпуса

SPECIFICATIONS

Material:	Алюминий
Finish:	Anodized
Аксессуар Тип:	Передняя панель
Product Type:	Передняя панель

Table 1/2

Catalog Number	Rack Height	Rack Width	Глубина мм	Package Quantity	Front Finish	Rear Finish
30823-209	2U	42HP	3mm	1	Anodized	Anodized
30823-215	2U	84HP	3mm	1	Anodized	Anodized
30823-254	3U	28HP	3mm	1	Anodized	Anodized

CatalogNumber	Rack Height	Rack Width	Глубина мм	Package Quantity	Front Finish	Rear Finish
30823-257	3U	42HP	3mm	1	Anodized	Anodized
30823-224	3U	63HP	3mm	1	Anodized	Anodized
30823-260	3U	84HP	3mm	1	Anodized	Anodized
30823-269	4U	42HP	3mm	1	Anodized	Anodized
30823-227	4U	63HP	3mm	1	Anodized	Anodized
30823-272	4U	84HP	3mm	1	Anodized	Anodized
30823-230	6U	63HP	3mm	1	Anodized	Anodized
30823-284	6U	84HP	3mm	1	Anodized	Anodized

Table 2/2					
Catalog Number	Treated Edges	EMC Shielding	Высота мм	Ширина мм	Quick Ship
30823-209	Нет	Нет	84mm	238.7mm	No
30823-215	Нет	Нет	84mm	452.1mm	No
30823-254	Нет	Нет	128.4mm	167.5mm	No
30823-257	Нет	Нет	128.4mm	238.7mm	No
30823-224	Нет	Нет	128.4mm	345.4mm	No
30823-260	Нет	Нет	128.4mm	452.1mm	No
30823-269	Нет	Нет	1729mm	238.7mm	No
30823-227	Нет	Нет	172.9mm	345.4mm	No
30823-272	Нет	Нет	172.9mm	452.1mm	No

Catalog Number	Treated Edges	EMC Shielding	Высота мм	Ширина мм	Quick Ship
30823-230	Нет	Нет	261.8mm	345.4mm	No
30823-284	Нет	Нет	261.8mm	452.1mm	No

ADDITIONAL PRODUCT DETAILS

Комплект для сборки одной задней и одной передней панели входит в комплект поставки.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE