

Countersunk Head Screw, Torx

Винты с потайной головкой.



CERTIFICATIONS



FEATURES

Винт для монтажа передней панели на сменном блоке каркасного типа в блочном каркасе (EuropacPRO)

SPECIFICATIONS

Type: Countersunk Screw

Product Type: Screw

Table 1/2

Catalog Number	Длина мм	Material	Finish	Package Quantity	Thread Size	Product Family
24812-751	6mm	Нержавеющая сталь		100	M2.5	
21191-589	8mm	Сталь	Nickel Plated	100	M3	
24812-501	20mm	Сталь	Nickel Plated	100	M3	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO

Table 2/2

Catalog Number	Works With	Certifications	Quick Ship
24812-751	Блочный каркас, Coffrets, Chassis		No
21191-589	Передние панели		No
24812-501	Блочный каркас, Coffrets, Chassis	RoHS	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE