

Датчик цифровых контактов для устройства Guardian Management Gateway



External sensor monitoring digital inputs with 2 RJ45 connectors. До 16 датчиков могут быть последовательно связаны коммутационным кабелем и подключены к одному порту управления Guardian.

FEATURES

Внешний датчик для шлюза Guardian Management Gateway

Один порт шлюза способен отслеживать до 16 сенсорных устройств с общей длиной кабеля 40 м.

Если датчик подключен к nVent SCHROFF Guardian, он отобразится в веб-интерфейсе с указанием типа и серийного номера

Пластмассовый корпус

Простой монтаж

Соединение 2 x RJ 45

Простое подключение по цепочке (daisy-chain) коммутационным кабелем CAT6 (или кабелем с более сильным экранированием)

SPECIFICATIONS

Table 1/1

Catalog Number	Type	Works With	Package Quantity	Quick Ship
21070-124	Digital Contact	Guardian Management Gateway	1	No
21070-125	Digital Contact	Guardian Management Gateway	1	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE