We connect and protect

VME64x System, Tower, 5 U, Pluggable PSU

CATALOG NUMBER

10836-045





Система Tower для VME64 7 печатных плат VME64x, высота 6 U, 160 мм. Питание системы осуществляется от сменного источника питания. Модуль управления вентилятором контролирует работу вентиляторов, следит за температурой и напряжением.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- Система в соответствии с IEC 60297-3-101, 102, 103; IEEE 1101.1, 1101.10/11; объединительная плата соответствует требованиям VITA 1.1-1997
- сменный источник питания, 19-дюймовый форм-фактор, 250 Вт; дополнительно возможна установка второго блока питания
- Отвод тепла 2 вентиляторами, воздушный поток направляется спереди назад; управляется модулем управления вентилятором (FCM) в зависимости от температуры
- Система для вертикального крепления печатных плат с учетом формата платы, 6 U, Глубина 160 мм; опция расположения вводов-выводов на задней панели
- Модуль индикации рабочего напряжения (пост. ток), аварийные сигналы от вентиляторов и датчиков температуры
- Возможность установки 5,25" DVD-дисковода
- Backplane VME64x 7 slot, 6 U, J1/J2 monolithic without P0 connector, Rear I/O option, in accordance with VITA 1-1994 and 1.1-1997

PRODUCT ATTRIBUTES

Product Type: System

Number of Slots: 7

Type: Корпус Tower

Backplane Type: 6 U VME64 Extension

Data Transfer: VME64; VME2eSST

Power per Slot: 30W

Input Voltage AC: 100 – 240V

Airflow Direction: Front to Rear

Rack Height: 10U

Power Supply Type: (1) Pluggable PSU

Power Supply Included: Да

Rear I/O: Да

Complies With: ANSI/VITA 1.1-1997

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Модифицированные системы доступны по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.