


Комплект сменных модулей для FMC с черной ручкой IEL, U-образная лицевая панель, экранированная (текстильная ЭМЗ прокладка), 6 U, 4 HP

CATALOG NUMBER

20836-254



Передняя накладка FMC соответствует спецификации Vita 57,1. Закрывает вырез на общей передней панели.

CERTIFICATIONS



FEATURES

В соответствии со спецификацией VITA 57.1

Для одиночного модуля 69,0 x 76,5 мм или двойного модуля 139,0 x 76,5 мм

PRODUCT ATTRIBUTES

Rack Height: 6U

Package Quantity: 1

Handle Type: IEL

Mounting: Screw-on Front

EMC Gasket Type: Textile

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: Нет

Complies With: Мезионная FMC, Vita 57.1

EMC Shielding: Да

Finish: Anodized; Passivated

Высота мм: 261.8mm

Material: Алюминий

Product Type: Передняя панель

Rack Width: 4HP

Type: Front Panel with Handle (PIU)

Ширина мм: 20mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE