



Комплект передней панели, экранированный, нижнее крепление на петлях, высота 3 U, ширина стойки 42 HP

CATALOG NUMBER

20848-599



Передняя панель из U-образного профиля откидывается снизу для установки текстильного уплотнителя.

CERTIFICATIONS



FEATURES

Передняя панель из U-образного профиля откидывается под углом 135° (кроме RatiopacPRO)

Позволяет выполнять монтаж на горизонтальных рейках

с экранированием, передняя панель из U-образного профиля с текстильным ЭМС-уплотнителем

Подходит для блочных каркасов EuropacPRO и корпусов RatiopacPRO, PropacPRO, CompacPRO)

PRODUCT ATTRIBUTES

Rack Height: 3U

Аксессуар Тип: Передняя панель

Rack Width: 42HP

Package Quantity: 1

Mounting: Hinged, Bottom

EMC Gasket Type: Textile

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: Нет

Complies With: IEC 60297-3-101; IEEE 1101.1/10

Глубина мм (D): 2.5mm

EMC Shielding: No (Retrofittable)

Finish: Anodized; Passivated

Высота мм (H): 128.4mm

Material: Алюминий

Product Type: Передняя панель

Type: Front Panel without Handle

Ширина мм (W): 213mm

Gross Weight: 0.296kg

ADDITIONAL PRODUCT DETAILS

Передняя панель снимается в открытом состоянии (> 135°)

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE