

# Винт с полукруглой головкой, Torx, оцинкованная сталь, самофиксирующаяся&nbsp;резьба, M2.5 x 6 мм

## CATALOG NUMBER

**24560-159**



Винты со сферо-цилиндрической головкой Torx с различной метрической резьбой и различной длины. С дополнительными функциями, такими как заземление или самоконтрящаяся резьба.

## CERTIFICATIONS



## FEATURES

Винт со сферо-цилиндрической головкой с Torx, самостопорящийся

## PRODUCT ATTRIBUTES

Длина мм: 6mm

Finish: Zinc Plated

Package Quantity: 100

Thread Size: M2.5

Material: Сталь

Product Type: Screw

Type: Panhead Screw

Works With: Backplanes; Test Adapters

## ADDITIONAL PRODUCT DETAILS

Макс. момент затяжки 0,2 Нм

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**