

Универсальный теплопроводник (FHC) Interscale, 20 мм

CATALOG NUMBER

24830-005



Расширение и сжатие теплопроводного блока по вертикали компенсирует наложение допусков и обеспечивает оптимальный поверхностный контакт и давление вдоль канала теплоотвода, что позволяет обойтись без теплопроводящей подложки.

CERTIFICATIONS



FEATURES

Поддержка процессоров Intel,, AMD, Via,, Freescale,, Поддержка процессоров NVidia и Texas Instrument для цоколей BGA

Непревзойденная эффективность кондуктивного охлаждения, Повышение эффективности на 10% по сравнению с традиционными методами кондуктивного охлаждения

Система кондуктивного охлаждения для компактного электронного оборудования Small Form Factor (подана заявка на патент)

Крепление к печатной плате с помощью теплопроводной клейкой ленты

Расширение и сжатие теплопроводного блока по вертикали компенсирует наложение допусков и обеспечивает оптимальный поверхностный контакт и давление вдоль канала теплоотвода, что позволяет обойтись без теплопроводящей подложки

Подходит для корпусов Interscale C

PRODUCT ATTRIBUTES

Product Type: Conductor Block

Product Family: Interscale

Type: Heat Conductor

Works With: Coffrets

Package Quantity: 1

Глубина мм: 22mm

Ширина мм: 22mm

Finish: Anodized; Aluminum-Zinc Plated

Gross Weight: 0.074kg

Material: Алюминий; Сталь

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE