



Горизонтальная рейка, задняя, тип L-ST, облегченного типа, стандартная, 84 HP

CATALOG NUMBER

34560-484



Combinations of horizontal rails and side panels

		"A" = yes, be combined. "N" = combination not recommended			
Rail type	Standard L	-	+	+	+
	Standard H	+	+	+	+
Side panel	Standard L	+	+	-	-
	Standard H	+	+	-	-
Standard L Standard H Standard L Standard H					

Горизонтальная рейка, тип ST, обеспечивает изолированный монтаж объединительной платы. Изоляция выполняется с использованием изоляционной полоски.

CERTIFICATIONS



FEATURES

Для монтажа объединительной платы с изолирующей полосой

Установка сверху и снизу

Алюминиевый экструдированный профиль, анодированная поверхность, электропроводящая контактная поверхность

PRODUCT ATTRIBUTES

Rack Width: 84HP
Package Quantity: 1
Finish: Anodized
Длина мм: 431.8mm
Material: Алюминий
Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO
Product Type: Горизонтальный рельс
Type: Light, ST
Works With: Блочный каркас; Coffrets

ADDITIONAL PRODUCT DETAILS

Поставка исключительно в размере товарной партии. Цена указана за отдельную единицу.

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	+971.4.378.1700
Chat with us:	Betschdorf, France	Qingdao, China	Bangalore, India
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	+91.80.6715.2001
	Warsaw, Poland	Singapore	Istanbul, Turkey
	+48.22.209.98.35	+65.6768.5800	+90.216.250.7374
	Assago, Italy	Shin-Yokohama, Japan	Chat with us:
	+39.02.932.7141	+81.45.476.0271	nvent.com/schroff
	Chat with us:	Chat with us:	
	nvent.com/schroff	nvent.com/schroff	



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE