


Телескопическая направляющая узкая, длина 559 мм

CATALOG NUMBER

60110-440



Узкая телескопическая направляющая для блочных каркасов с удлинением > 100 %.

CERTIFICATIONS



FEATURES

Подходит для блочных каркасов шириной 84 HP (тип F, тип H, тип L)

Стопорение при полном выдвижении

откидная

Длина выдвижения > 100 %

Ширина рейки 7,5 мм

Максимальная габаритная ширина выдвижения/выдвижного ящика w = 84 HP (435 мм)

PRODUCT ATTRIBUTES

Длина мм: 559mm

Package Quantity: 2

Finish: Zinc Plated

Material: Сталь

Product Type: Telescopic Slide

Static Load: 15kg

Type: Narrow

ADDITIONAL PRODUCT DETAILS

Для установки на 19-дюймовой панели необходимо дополнительно заказать монтажный комплект.

Телескопическая направляющая может быть установлена только на блочном каркасе без установленного заднего углового профиля или модифицированного заднего углового профиля (со специальным вырезом).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE