

передняя панель, возможно дооснащение экранированием



Плоская передняя панель. Возможность экранирования с помощью ЭМС-прокладки из нержавеющей стали.

CERTIFICATIONS



FEATURES

Для ЭМС-прокладки из нержавеющей стали

алюминий, 2,5 мм, лицевая поверхность анодированная, токопроводящая

SPECIFICATIONS

Глубина мм (D):	2.5mm
Material:	Алюминий
Аксессуар Тип:	Передняя панель
Product Type:	Передняя панель
Type:	Front Panel without Handle
EMC Shielding:	No (Retrofittable)

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
20846-425	3U	3HP	1	Screw-on Front	Anodized	Conductive

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30846-865	6U	2HP	1	Screw-on Front	Anodized	Conductive
20846-426	3U	4HP	1	Screw-on Front	Anodized	Conductive
20846-427	3U	5HP	1	Screw-on Front	Anodized	Conductive
20846-428	3U	6HP	1	Screw-on Front	Anodized	Conductive
20846-429	3U	7HP	1	Screw-on Front	Anodized	Conductive
20846-443	6U	4HP	1	Screw-on Front	Anodized	Conductive
20846-430	3U	8HP	1	Screw-on Front	Anodized	Conductive
20846-442	6U	3HP	1	Screw-on Front	Anodized	Conductive
20846-431	3U	10HP	1	Screw-on Front	Anodized	Conductive
20846-444	6U	5HP	1	Screw-on Front	Anodized	Conductive
20846-432	3U	12HP	1	Screw-on Front	Anodized	Conductive
20846-445	6U	6HP	1	Screw-on Front	Anodized	Conductive
20846-433	3U	14HP	1	Screw-on Front	Anodized	Conductive
20846-446	6U	7HP	1	Screw-on Front	Anodized	Conductive
20846-424	3U	16HP	1	Screw-on Front	Anodized	Conductive
20846-447	6U	8HP	1	Screw-on Front	Anodized	Conductive
20846-448	6U	10HP	1	Screw-on Front	Anodized	Conductive
20846-434	3U	21HP	1	Screw-on Front	Anodized	Conductive

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
20846-449	6U	12HP	1	Screw-on Front	Anodized	Conductive
20846-436	3U	28HP	1	Screw-on Front	Anodized	Conductive
20846-450	6U	14HP	1	Screw-on Front	Anodized	Conductive
20846-456	6U	16HP	1	Screw-on Front	Anodized	Conductive
20846-451	6U	21HP	1	Screw-on Front	Anodized	Conductive
20846-437	3U	42HP	1	Screw-on Front	Anodized	Conductive
30846-588	2U	84HP	1	Screw-on Front	Anodized	Conductive
20846-452	6U	28HP	1	Screw-on Front	Anodized	Conductive
20846-438	3U	63HP	1	Screw-on Front	Anodized	Conductive
30846-676	3U	84HP	1	Screw-on Front	Anodized	Conductive
20846-453	6U	42HP	1	Screw-on Front	Anodized	Conductive
30846-683	4U	84HP	1	Screw-on Front	Anodized	Conductive
20846-454	6U	63HP	1	Screw-on Front	Anodized	Conductive
30846-771	6U	84HP	1	Screw-on Front	Anodized	Conductive
30846-859	9U	84HP	1	Screw-on Front	Anodized	Conductive
30846-864	3U	2HP	1	Screw-on Front	Anodized	Conductive

Table 2/2

Catalog Number	Treated Edges	Complies With	Finish	Высота мм (H)	Ширина мм (W)	Quick Ship
----------------	---------------	---------------	--------	---------------	---------------	------------

20846-425	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	14.9mm	No
30846-865	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	9.8mm	No
20846-426	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	20mm	No
20846-427	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	25mm	No
20846-428	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	30.1mm	No
20846-429	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	35.2mm	No
20846-443	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	20mm	No
20846-430	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	40.3mm	No
20846-442	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	14.9mm	No
20846-431	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	50.5mm	No
20846-444	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	25mm	No
20846-432	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	60.6mm	No
20846-445	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	30.1mm	No
20846-433	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	70.8mm	No
20846-446	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	35.2mm	No

20846-424	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	80.9mm	No
20846-447	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	40.3mm	No
20846-448	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	50.5mm	No
20846-434	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	106.3mm	No
20846-449	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	60.6mm	No
20846-436	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	141.9mm	No
20846-450	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	70.8mm	No
20846-456	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	80.9mm	No
20846-451	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	106.3mm	No
20846-437	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	213mm	No
30846-588	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized, Passivated	84mm	426.4mm	No
20846-452	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	141.9mm	No
20846-438	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	319.7mm	No
30846-676	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized, Passivated	128.4mm	426.4mm	No
20846-453	Нет	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	213mm	No

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE