

Guide Rail With Coding for CompactPCI/ VME64x, поликарбонат



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

CERTIFICATIONS



FEATURES

НОВОЕ поколение с пластмассовыми направляющими кодирующего типа для надежной фиксации печатных плат или вставных блоков

Значительно повышенная устойчивость, благодаря оптимизированной конструкции и высококачественному материалу (поликарбонат)

«Не содержат галогенов», согласно IEC 61249-2-21

Могут быть закреплены на горизонтальных рельсах (алюминиевый экструдированный профиль) или на панелях толщиной 1,5 мм

Для более высоких требований в отношении ударных нагрузок и вибрации направляющие могут прикручиваться болтами к горизонтальной рейке (тип H и тип R)

Доступен дополнительный зажим ESD для проводящего контакта между печатной платой и горизонтальным рельсом

Температура хранения: от -40 °C до 130 °C

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

SPECIFICATIONS

Works With: Блочный каркас; Coffrets; 19" Chassis; Системы

Type: Coding

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac

Product Type: Направляющие рельсы

Table 1/2

Catalog Number	Material	Color	Package Quantity	Board Depth	Groove Width	Complies With
64568-089	Fiber-Reinforced Plastic	Красный	1	160mm	2	EN 45545-2
64568-090	Fiber-Reinforced Plastic	Серый	1	160mm	2	EN 45545-2
64568-109	Fiber-Reinforced Plastic, Алюминий	Красный, Серебристый	1	160mm	2.5	EN 45545-2
64568-110	Fiber-Reinforced Plastic, Алюминий	Серый, Серебристый	1	160mm	2.5	EN 45545-2
24568-357	Fiber-Reinforced Plastic	Красный	10	70mm	2	EN 45545-2
24568-360	Fiber-Reinforced Plastic	Серый	10	70mm	2	EN 45545-2
24568-358	Fiber-Reinforced Plastic	Серый	10	160mm	2	EN 45545-2
24568-356	Fiber-Reinforced Plastic	Красный	10	160mm	2	EN 45545-2
24568-341	Fiber-Reinforced Plastic, Алюминий	Серый, Серебристый	10	280mm	2.5	EN 45545-2
24568-331	Fiber-Reinforced Plastic, Алюминий	Красный, Серебристый	10	280mm	2.5	EN 45545-2
24568-332	Fiber-Reinforced Plastic, Алюминий	Красный, Серебристый	10	340mm	2.5	EN 45545-2

CatalogNumber	Material	Color	Package Quantity	Board Depth	Groove Width	Complies With
24568-342	Fiber-Reinforced Plastic, Алюминий	Серый, Серебристый	10	340mm	2.5	EN 45545-2
64568-085	Fiber-Reinforced Plastic	Красный	1	70mm	2	EN 45545-2
64568-086	Fiber-Reinforced Plastic	Серый	1	70mm	2	EN 45545-2
64568-091	Fiber-Reinforced Plastic	Красный	1	220mm	2	EN 45545-2
64568-092	Fiber-Reinforced Plastic	Серый	1	220mm	2	EN 45545-2
64568-111	Fiber-Reinforced Plastic, Алюминий	Красный, Серебристый	1	220mm	2.5	EN 45545-2
64568-112	Fiber-Reinforced Plastic, Алюминий	Серый, Серебристый	1	220mm	2.5	EN 45545-2

Table 2/2

Catalog Number	Finish	Quick Ship
64568-089		No
64568-090		No
64568-109		No
64568-110		No
24568-357		No
24568-360		No
24568-358		No

Catalog Number	Finish	Quick Ship
24568-356		No
24568-341	Anodized	No
24568-331	Anodized	No
24568-332	Anodized	No
24568-342		No
64568-085		No
64568-086		No
64568-091		No
64568-092		No
64568-111		No
64568-112		No

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE