


Наконечник направляющей, поликарбонат

Plastic end pieces for individual multi-piece guide rails with plastic or Aluminum extrusion mid-piece. Available as type Standard or Accessory.



CERTIFICATIONS



FEATURES

Наконечники (ПК) для отдельных составных направляющих со средней секцией из пластика или экструдированного алюминия

«Не содержат галогенов», согласно IEC 61249-2-21

Средние секции, доступные для печатных плат стандартной длины (160, 220, 280 и 340 мм) и особых размеров, таких как вариант длиной 1000 мм

Могут быть закреплены на горизонтальных рельсах (алюминиевый экструдированный профиль) или на панелях толщиной 1,5 мм

Могут крепиться винтами для более высоких требований к устойчивости к ударным нагрузкам и вибрации

Доступен дополнительный зажим ESD для проводящего контакта между печатной платой и горизонтальным рельсом

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

SPECIFICATIONS

Works With:	Блочный каркас; Coffrets; Chassis
Product Family:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Material:	Fiber-Reinforced Plastic
Product Type:	Rail End Piece

Table 1/1

Catalog Number	Package Quantity	Complies With	Type	Package Unit	Groove Width	Quick Ship
64568-018	1	EN 45545-2	Accessory	Pair	2.5	No
64568-004	1	EN 45545-2	Standard	Pair	2	No
64568-014	1	EN 45545-2	Standard	Pair	2.5	No
64568-093	1	EN 45545-2	Coding Peg	Pair	2.5	No
64568-094	1	EN 45545-2	Coding Peg	Pair	2.5	No
64568-095	1	EN 45545-2	Coding Peg	Pair	2.5	No
64568-008	1	EN 45545-2	Accessory	Pair	2	No

ADDITIONAL PRODUCT DETAILS

Поставка исключительно в размере товарной партии. Цена указана за отдельную единицу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE