


Изоляционная планка горизонтальной рейки



Планка обеспечивает изолированный монтаж объединительных плат или металлических панелей в качестве опор для разъемов. Создает стандартизированную монтажную глубину для вставных блоков в блочном каркасе в сочетании с горизонтальными рельсами L-ST и H-ST. Подходит для RatiopacPRO/-AIR, Propac Pro, CompacPRO и EuropacPRO/-Rugged.

CERTIFICATIONS



FEATURES

Для изолированного монтажа объединительных плат или металлических панелей в качестве опор для разъемов

Создает стандартизированную монтажную глубину для вставных блоков в блочном каркасе в сочетании с горизонтальными рельсами L-ST и H-ST

SPECIFICATIONS

Works With:	Блочный каркас; Coffrets
Product Family:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac
Product Type:	Insulation Strip
Material:	Polycarbonate

Table 1/1

Catalog Number	Rack Width	Package Quantity	Flammability Rating	Длина мм	Quick Ship
24560-820	20HP	10	UL® 94V-0	101.5mm	No
24560-828	28HP	10	UL® 94V-0	144.2mm	No

Catalog Number	Rack Width	Package Quantity	Flammability Rating	Длина мм	Quick Ship
24560-840	40HP	10	UL® 94V-0	205.12mm	No
24560-842	42HP	10	UL® 94V-0	210.4mm	No
24560-863	63HP	10	UL® 94V-0	316.88mm	No
24560-884	84HP	10	UL® 94V-0	428.64mm	No

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE