

Настольный корпус Interscale, Без перфорации



Гибкий настольный корпус с интегрированной защитой от электромагнитных помех. На основе платформы nVent SCHROFF Interscale и в соответствии с IEC 60297-3-109.

CERTIFICATIONS



FEATURES

Настольный модульный корпус, состоящий из 4 компонентов

Разработано в соответствии с IEC 60297-3-109 (в стадии разработки IEC)

Встроенная защита от ЭМС

Степень защиты от внешних воздействий — до IP 30

Цвет RAL 7016

Модифицированные или изготавливаемые по спецификации заказчика корпуса доступны по запросу

SPECIFICATIONS

Material:	Алюминий; Сталь
Type:	Настольный корпус
Product Family:	Interscale
Protection Rating:	IP30
Color Code:	RAL 7016
Product Type:	Small Form Factor Case

Table 1/2

Catalog Number	Высота мм	Package Quantity	Ширина мм	Глубина мм	Cooling	Color
14820-133	43.7mm	1	132.6mm	132.6mm	Без перфорации	Anthracite Grey
14820-134	43.7mm	1	133mm	177mm	Без перфорации	Anthracite Grey
14820-154	43.7mm	1	221mm	177mm	Без перфорации	Anthracite Grey
14820-254	88.1mm	1	221mm	177mm	Без перфорации	Anthracite Grey
14820-155	43.7mm	1	221mm	221.45mm	Без перфорации	Anthracite Grey
14820-175	43.7mm	1	310mm	221.45mm	Без перфорации	Anthracite Grey
14820-195	43.7mm	1	399mm	221.45mm	Без перфорации	Anthracite Grey
14820-197	43.7mm	1	399mm	310.35mm	Без перфорации	Anthracite Grey
14820-255	88.1mm	1	221mm	221.45mm	Без перфорации	Anthracite Grey
14820-275	88.1mm	1	310mm	221.45mm	Без перфорации	Anthracite Grey
14820-295	88.1mm	1	399mm	221.45mm	Без перфорации	Anthracite Grey
14820-297	88.1mm	1	399mm	310.35mm	Без перфорации	Anthracite Grey
14820-375	132.6mm	1	310mm	221.45mm	Без перфорации	Anthracite Grey
14820-395	132.6mm	1	399mm	221.45mm	Без перфорации	Anthracite Grey
14820-397	132.6mm	1	399mm	310.35mm	Без перфорации	Anthracite Grey

Table 2/2

Catalog Number	Finish	Quick Ship
14820-133	Aluminum-Zinc Plated, Powder Coated	No

Catalog Number	Finish	Quick Ship
14820-134	Aluminum-Zinc Plated, Powder Coated	No
14820-154	Aluminum-Zinc Plated, Powder Coated	No
14820-254	Aluminum-Zinc Plated, Powder Coated	No
14820-155	Aluminum-Zinc Plated, Powder Coated	No
14820-175	Aluminum-Zinc Plated, Powder Coated	No
14820-195	Aluminum-Zinc Plated, Powder Coated	No
14820-197	Aluminum-Zinc Plated, Powder Coated	No
14820-255	Aluminum-Zinc Plated, Powder Coated	No
14820-275	Aluminum-Zinc Plated, Powder Coated	No
14820-295	Aluminum-Zinc Plated, Powder Coated	No
14820-297	Aluminum-Zinc Plated, Powder Coated	No
14820-375	Aluminum-Zinc Plated, Powder Coated	No
14820-395	Aluminum-Zinc Plated, Powder Coated	No
14820-397	Aluminum-Zinc Plated, Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE