


19-дюймовое шасси MultipacPRO, алюминий, для Eurocards в сборе



Это 19" шасси является блочным каркасом, пригодным для горизонтального монтажа печатных плат, а также для монтажа нестандартных компонентов, например, трансформаторов или других тяжелых компонентов, обычно устанавливаемых на шасси. Этот вариант предназначен для горизонтального монтажа печатной платы.

CERTIFICATIONS



FEATURES

Алюминиевая конструкция

Съемная передняя и задняя панели для удобства монтажа и доработки

IP 20 в соответствии с IEC 60529

Поставляется в компактной плоской упаковке

Возможны дополнительные изменения, например, дополнительные вырезы или отверстия, различные варианты отделки или размеры

Внутренние и внешние размеры соответствуют IEC 60297-3-100, -105

ЭМС-экранирование: до 20 дБ(А) при 2 ГГц без экранирующего материала. Свыше 40 дБ(А) при 1 ГГц с добавлением прокладки из нержавеющей стали между передней панелью и корпусом

Крышка и панель основания с просверленными отверстиями для горизонтального монтажа европлат

SPECIFICATIONS

Material:	Алюминий
Finish:	Anodized; Passivated
Product Family:	MultipacPRO

EMC Shielding: No (Retrofittable)
Type: Solid
Product Type: Subrack/Chassis

Table 1/1						
Catalog Number	Rack Height	Глубина мм	Usable Width	Mounting	Complies With	Quick Ship
20860-641	1U	220mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-101, IEC 60297-3-105	No
20860-642	1U	280mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-101, IEC 60297-3-105	No
20860-645	2U	280mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-101	No

ADDITIONAL PRODUCT DETAILS

Передние ручки заказываются отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America All locations +1.763.422.2661 Chat with us: nvent.com/schroff	Europe Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff	Asia Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff	Middle East & India Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff
---	---	---	---



Our powerful portfolio of brands:

CADDY
ERICO
HOFFMAN
ILSCO
SCHROFF
TRACHTE