

19-дюймовое шасси MultipacPRO, алюминий, верхняя крышка и основание перфорированные



Это 19" шасси является блочным каркасом, пригодным для горизонтального монтажа печатных плат, а также для монтажа нестандартных компонентов, например, трансформаторов или других тяжелых компонентов, обычно устанавливаемых на шасси. Этот вариант исполнения имеет перфорированные верхнюю и нижнюю крышки для оптимизации потока воздуха и отвода тепла.

CERTIFICATIONS



FEATURES

Алюминиевая конструкция

Съемная передняя и задняя панели для удобства монтажа и доработки

IP 20 в соответствии с IEC 60529

Поставляется в компактной плоской упаковке

Доступны модификации, включающие вырезы, различные варианты отделки или размеры

Внутренние и внешние размеры соответствуют IEC 60297-3-100, -105

ЭМС-экранирование: до 20 дБ(А) при 2 ГГц без экранирующего материала. Свыше 40 дБ(А) при 1 ГГц с добавлением прокладки из нержавеющей стали между передней панелью и корпусом

SPECIFICATIONS

Material:	Алюминий
Finish:	Anodized; Passivated
Product Family:	MultipacPRO

EMC Shielding: No (Retrofittable)

Type: С перфорацией

Product Type: Subrack/Chassis

Table 1/2

Catalog Number	Rack Height	Глубина мм	Usable Width	Mounting	Complies With	Certifications
20860-621	1U	220mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	RoHS
20860-622	1U	280mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	RoHS
20860-624	2U	220mm	403mm	Rack	IEC 60297-3-100	
20860-625	2U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-626	2U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-627	3U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-628	3U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-629	3U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-630	3U	460mm	403mm	Rack	IEC 60297-3-100	
20860-632	4U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-633	4U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-634	4U	460mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-635	5U	460mm	403mm	Rack	IEC 60297-3-100	RoHS

Table 2/2

Catalog Number	Quick Ship
20860-621	No

Catalog Number	Quick Ship
20860-622	No
20860-624	No
20860-625	No
20860-626	No
20860-627	No
20860-628	No
20860-629	No
20860-630	No
20860-632	No
20860-633	No
20860-634	No
20860-635	No

ADDITIONAL PRODUCT DETAILS

Передние ручки заказываются отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE