

19-дюймовый источник питания перемен. тока/пост. тока Maxpower, 100 Вт, одинарный, Настраиваемый



Pluggable 19" Power Supplies with H15 connector for fanless applications. С широким диапазоном входного переменного тока и одним регулируемым выходным напряжением.

CERTIFICATIONS



FEATURES

Широкий диапазон входного напряжения: 90 ... 264 В перемен. тока и 100 ... 360 В пост. тока с активной коррекцией коэффициента мощности (PFC)

1 выходное напряжение

Сигнал "Выходное напряжение ОК"

Широкий диапазон регулировки выходного напряжения

Встроенный развязывающий диод для обеспечения резервирования

Равномерное распределение тока в параллельном режиме работы (CSB)

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Input Voltage AC	Input Voltage DC	Мощность W	Number of Output Voltages	Voltage 1
----------------	------	------------------	------------------	------------	---------------------------	-----------

13100-134	19" Switched-Mode	90 – 264V		102W	1	16V
13100-133	19" Switched-Mode	90 – 264V	100 – 360V	100W	1	4.5V

Table 2/2						
Catalog Number	Current 1	Rack Height	Rack Width	Глубина мм	Package Quantity	Quick Ship
13100-134	3.4A	3U	6HP	171.93mm	1	No
13100-133	5.9A	3U	6HP	171.93mm	1	No

ADDITIONAL PRODUCT DETAILS

Передняя панель заказывается отдельно.

Выходные данные при напряжении сети 190 В перем. тока, Ta=0 ... 50°C.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE