

19-дюймовый источник питания перем. тока/пост. тока Maxpower, 100 Вт, Тройной



Pluggable 19" Power Supplies with H15 connector for fanless applications. С широким диапазоном входного переменного тока и тремя выходными напряжениями.

CERTIFICATIONS



FEATURES

Широкий диапазон входного напряжения 90 ... 254 В перем. тока и 100 ... 360 В пост. тока с активной коррекцией коэффициента мощности (PFC)

3 выходных напряжения

Сигнал "Выходное напряжение ОК"

Высокая удельная мощность

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Input Voltage AC	Мощность W	Number of Output Voltages	Voltage 1	Current 1
13100-122	19" Switched-Mode	90 – 264V	100W	3	5V	8A
13100-123	19" Switched-Mode	90 – 264V	100W	3	5V	8A

Table 2/3						
Catalog Number	Voltage 2	Current 2	Voltage 3	Current 3	Rack Height	Rack Width
13100-122	12V	2.5A	12V	2.5A	3U	8HP
13100-123	15V	2A	15V	2A	3U	8HP

Table 3/3			
Catalog Number	Глубина мм	Package Quantity	Quick Ship
13100-122	171.93mm	1	No
13100-123	171.93mm	1	No

ADDITIONAL PRODUCT DETAILS

Передняя панель заказывается отдельно.

Выходные данные при напряжении сети >190 В перем. тока, Ta = -25 ... 50°C.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE