

19-дюймовый источник питания перем./пост. тока Maxpower 50 Вт, одинарный



Резервирование при включенной ИЛИ отключенной системе. Базовая нагрузка не требуется. Автоматическое распределение нагрузки в зависимости от температуры источника питания. Не требуется линия распределения тока между источниками питания. Квазирезонансная топология уменьшает электромагнитное излучение.

CERTIFICATIONS



FEATURES

Широкий диапазон входного напряжения 90 ... 253 В перем. тока и 100 ... 360 В пост. тока

1 выходное напряжение

Сигнал "Выходное напряжение ОК"

Передняя панель включена

Потребление мощности в режиме ожидания (нулевая нагрузка) <1,5 Вт

КПД до 88 %

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Input Voltage AC	Мощность W	Number of Output Voltages	Voltage 1	Current 1
----------------	------	------------------	------------	---------------------------	-----------	-----------

13100-174	19" Switched-Mode	90 – 264V	53W	1	48V	1.1A
13100-172	19" Switched-Mode	90 – 264V	50W	1	15V	3.4A
13100-173	19" Switched-Mode	90 – 264V	50W	1	24V	2.1A
13100-170	19" Switched-Mode	90 – 253V	50W	1	5V	10A
13100-171	19" Switched-Mode	90 – 264V	50W	1	12V	4.2A

Table 2/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
13100-174	3U	6HP	1	No
13100-172	3U	6HP	1	No
13100-173	3U	6HP	1	No
13100-170	3U	6HP	1	No
13100-171	3U	6HP	1	No

ADDITIONAL PRODUCT DETAILS

Выходные данные на уровне Ta= -25 ... 50 °C.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE