

# панель электропитания, IEC C19



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Распределительный блок питания на алюминиевом шасси размером 1 U x 1 U легко интегрируется в стойку с розетками IEC C19.

## CERTIFICATIONS



## FEATURES

Панель электропитания с розетками C19 IEC

При установке панель электропитания можно развернуть в любую сторону (с шагом 90°)

Сетевой кабель 2 м, с разъемом в соответствии с IEC 60309

Монтажная высота 1 U

Монтажная высота 1 U

## SPECIFICATIONS

|                      |                       |
|----------------------|-----------------------|
| <b>Material:</b>     | Алюминий; Polyamide   |
| <b>Color:</b>        | Серый                 |
| <b>Product Type:</b> | Панели электропитания |

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Package Quantity | Глубина мм |
|----------------|-------------|-----------------|------------------|------------|------------------|------------|
| 60110-280      | IEC C19     | 8               | Нет              | 230V       | 1                | 44mm       |

| CatalogNumber | Socket Type | SocketQuantity | Switched Outlets | Voltage AC | Package Quantity | Глубина мм |
|---------------|-------------|----------------|------------------|------------|------------------|------------|
| 60110-282     | IEC C19     | 12             | Нет              | 230V       | 1                | 44mm       |
| 60110-281     | IEC C19     | 12             | Нет              | 230V       | 1                | 44mm       |

| Table 2/2      |          |           |          |            |
|----------------|----------|-----------|----------|------------|
| Catalog Number | Finish   | Высота мм | Длина мм | Quick Ship |
| 60110-280      | Anodized | 44mm      | 438.5mm  | No         |
| 60110-282      | Anodized | 44mm      | 947.5mm  | No         |
| 60110-281      | Anodized | 44mm      | 947.5mm  | No         |

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE