

панель электропитания, SCHUKO



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Распределительный блок питания на алюминиевом шасси размером 1 U x 1 U легко интегрируется в шкаф с розетками Schuko.

CERTIFICATIONS



FEATURES

230 V, 16 A

Горизонтальная или вертикальная установка

Соединительный кабель 2 м с вилкой SCHUKO/UTE

В соответствии с DIN 57620, VDE 0620

Высота установки 1 U

Панели электропитания с гнездами SCHUKO

При установке панель электропитания можно развернуть в любую сторону (с шагом 90°)

SPECIFICATIONS

Material:	Алюминий; Polyamide
Color:	Серый
Product Type:	Панели электропитания

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
----------------	-------------	-----------------	------------------	------------	----------	------------------

60110-200	SCHUKO	3	Нет	230V		1
60110-201	SCHUKO	4	Нет	230V		1
60110-202	SCHUKO	9	Нет	230V		1
60110-206	SCHUKO	8	Да	230V		1
60110-210	SCHUKO	8	Нет	230V	Transient Protection	1
60110-214	SCHUKO	7	Нет	230V	Mains Suppression Filter	1
60110-266	SCHUKO	6	Нет	230V	Transient Protection, Mains Suppression Filter	1
60110-203	SCHUKO	12	Нет	230V		1
60110-204	SCHUKO	15	Нет	230V		1
60110-205	SCHUKO	19	Нет	230V		1
60110-207	SCHUKO	12	Да	230V		1
60110-208	SCHUKO	15	Да	230V		1
60110-209	SCHUKO	19	Да	230V		1
60110-211	SCHUKO	9	Нет	230V	Transient Protection	1
60110-212	SCHUKO	6	Нет	230V	Overcurrent Protection	1
60110-216	SCHUKO	6	Нет	230V	Fault Current Protection	1
60110-217	SCHUKO	6	Нет	230V	Fault Current Protection, Overcurrent Protection	1

Table 2/2

Catalog Number	Глубина мм	Finish	Длина мм	Quick Ship
60110-200	44mm	Anodized	184mm	No
60110-201	44mm	Anodized	210mm	No
60110-202	44mm	Anodized	438.5mm	No
60110-206	44mm	Anodized	438.5mm	No
60110-210	44mm	Anodized	438.5mm	No
60110-214	44mm	Anodized	438.5mm	No
60110-266	44mm	Anodized	438.5mm	No
60110-203	44mm	Anodized	947.5mm	No
60110-204	44mm	Anodized	1202mm	No
60110-205	44mm	Anodized	1753mm	No
60110-207	44mm	Anodized	947.5mm	No
60110-208	44mm	Anodized	1202mm	No
60110-209	44mm	Anodized	1753mm	No
60110-211	44mm	Anodized	947.5mm	No
60110-212	75mm	Anodized	438.5mm	No
60110-216	88mm	Anodized	438.5mm	No
60110-217	88mm	Anodized	438.5mm	No

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE