

# Телескопическая направляющая Universal, 1 U

Телескопическая направляющая Universal с удлинением > 100 % и несущей способностью до 39 кг.



## CERTIFICATIONS



## FEATURES

Для боковой установки на 19" монтажный профиль (19" системная перфорация остается свободной для монтажа полок и ящиков)

Допустимая статическая нагрузка на пару 23 - 39 кг

С возможностью расцепления

Длина выдвижения > 100 %

Ширина направляющей k = 9,7 мм, макс. монтажная ширина выдвижной полки/выдвижного ящика w = 429 мм

## SPECIFICATIONS

|                      |                  |
|----------------------|------------------|
| <b>Material:</b>     | Сталь            |
| <b>Product Type:</b> | Telescopic Slide |
| <b>Finish:</b>       | Zinc Plated      |

Table 1/1

| Catalog Number | Длина мм | Package Quantity | Static Load | Type | Quick Ship |
|----------------|----------|------------------|-------------|------|------------|
|----------------|----------|------------------|-------------|------|------------|

|           |       |   |      |           |    |
|-----------|-------|---|------|-----------|----|
| 20110-090 | 356mm | 2 | 39kg | Universal | No |
| 20110-091 | 406mm | 2 | 36kg | Universal | No |
| 20110-092 | 457mm | 2 | 34kg | Universal | No |
| 20110-093 | 508mm | 2 | 32kg | Universal | No |
| 20110-094 | 559mm | 2 | 29kg | Universal | No |
| 20110-095 | 610mm | 2 | 27kg | Universal | No |
| 20110-096 | 660mm | 2 | 23kg | Universal | No |
| 20110-097 | 711mm | 2 | 23kg | Universal | No |

## ADDITIONAL PRODUCT DETAILS

Телескопические рейки Universal также могут быть установлены без дополнительных компонентов в нестандартных системах, отличных от 19-дюймовых шкафов.

Для установки на 19-дюймовой панели необходимо дополнительно заказать монтажный комплект.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**