

Телескопическая направляющая Universal, Тонкие конструктивные элементы, 2 U

Узкая универсальная телескопическая направляющая,
2 U.



CERTIFICATIONS



FEATURES

Ширина направляющей $k = 9,7$ мм, макс. установочная ширина расширения/выдвижного ящика $w = 429$ мм

Для боковой установки на 19" монтажный профиль (19" системная перфорация остается свободной для монтажа полок и ящиков)

Блокировка при полном выдвижении

Допустимая статическая нагрузка на пару 46 - 57 кг

Длина выдвижения $> 110\%$

SPECIFICATIONS

Material:	Сталь
Product Type:	Telescopic Slide
Finish:	Zinc Plated

Table 1/1

Catalog Number	Длина мм	Package Quantity	Static Load	Type	Quick Ship
----------------	----------	------------------	-------------	------	------------

20110-071	356mm	2	57kg	Universal	No
20110-074	508mm	2	55kg	Universal	No
20110-077	610mm	2	46kg	Universal	No
20110-073	457mm	2	55kg	Universal	No
20110-075	559mm	2	46kg	Universal	No
20110-072	406mm	2	55kg	Universal	No
20110-076	584mm	2	46kg	Universal	No

ADDITIONAL PRODUCT DETAILS

Телескопические рейки Universal также могут быть установлены без дополнительных компонентов в нестандартных системах, отличных от 19-дюймовых шкафов.

Для установки на 19-дюймовой панели необходимо дополнительно заказать монтажный комплект.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE