


Ручка для лотка

Ручку лотка можно зафиксировать в вырезе на боковой панели корпуса. Доступны 2 размера.



CERTIFICATIONS



FEATURES

Допустимая статическая нагрузка 30 кг/пара

Минимальная толщина боковой панели 1,0 мм

SPECIFICATIONS

Static Load:	30kg
Color:	Черный
Works With:	Coffrets
Product Family:	RatiopacPRO; RatiopacPRO AIR; PropacPRO; CompacPRO; Comptec
Product Type:	Ручка
Material:	Polycarbonate
Type:	Static

Table 1/2

Catalog Number	Высота мм	Ширина мм	Глубина мм	Package Quantity	Handle Type	Flammability Rating
60225-012	79mm	187mm	22mm	1	Tray Handle	UL® 94V-0

CatalogNumber	Высота мм	Ширина мм	Глубина мм	Package Quantity	Handle Type	Flammability Rating
60229-004	56mm	110mm	18mm	1	Tray Handle	UL® 94V-0

Table 2/2

Catalog Number	Quick Ship
60225-012	No
60229-004	No

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

Продукция имеющая маркировку упаковочной единицы, упаковывается заранее и хранится на складе для своевременной отправки заказчику. Количество при заказе, отличное от размера товарной партии (напр. 2 шт.), округляется до размера товарной партии или его кратного значения

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE