

Varistar CP Perforated Door, Seismic IP20, Multi-Point Locking



IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

FEATURES

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

SPECIFICATIONS

Product Type: Cabinet Door

Protection Rating: IP20

Material: Сталь

Table 1/2

Catalog Number	Rack Height	Высота мм	Ширина мм	Package Quantity	Color	Color Code
21630-876	33U	1600mm	600mm	1	Black Grey	RAL 7021
21630-877	33U	1600mm	800mm	1	Black Grey	RAL 7021
21630-878	38U	1800mm	600mm	1	Black Grey	RAL 7021
21630-879	38U	1800mm	800mm	1	Black Grey	RAL 7021

CatalogNumber	Rack Height	Высота мм	Ширина мм	Package Quantity	Color	Color Code
21630-880	42U	2000mm	600mm	1	Black Grey	RAL 7021
21630-881	42U	2000mm	800mm	1	Black Grey	RAL 7021
21630-882	47U	2200mm	600mm	1	Black Grey	RAL 7021
21630-883	47U	2200mm	800mm	1	Black Grey	RAL 7021

Table 2/2

Catalog Number	Complies With	Finish	Locking Type	Type	Works With	Quick Ship
21630-876	IEC 61587-1, IEC 61587-2	Powder Coated	4-Point Locking	Steel Door, Perforated	Varistar CP	No
21630-877	IEC 61587-1, IEC 61587-2	Powder Coated	4-Point Locking	Steel Door, Perforated	Varistar CP	No
21630-878	IEC 61587-1, IEC 61587-2	Powder Coated	4-Point Locking	Steel Door, Perforated	Varistar CP	No
21630-879	IEC 61587-1, IEC 61587-2	Powder Coated	4-Point Locking	Steel Door, Perforated	Varistar CP	No
21630-880	IEC 61587-1, IEC 61587-2	Powder Coated	4-Point Locking	Steel Door, Perforated	Varistar CP	No
21630-881	IEC 61587-1, IEC 61587-2	Powder Coated	4-Point Locking	Steel Door, Perforated	Varistar CP	No
21630-882	IEC 61587-1, IEC 61587-2	Powder Coated	5-Point Locking	Steel Door, Perforated	Varistar CP	No
21630-883	IEC 61587-1, IEC 61587-2	Powder Coated	5-Point Locking	Steel Door, Perforated	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE