



# PEKPSM Power Switch Mount Pyramid Equipment Support

Power Switch Box Mount Bolt Spacing	
BS1	BS2
2 9/16" Min - 5 1/8" Max	4" Min - 8.5" Max





Power Switch Box (Not Included)

1/4-20 Fasteners Included



## Horizontal Mounting Strut or Steel Tube Profile



- WARNING:**
- nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at [www.nVent.com](http://www.nVent.com) and from your nVent customer service representative.
  - nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
  - All instructions must be completely followed to ensure proper and safe installation and performance.
  - Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.
  - Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.
  - All pipe supports, hangers, intermediate components and structural attachments must ONLY be used as described herein and are NEVER to be used for any other purpose.

**NOTE:** All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:


- Conformance to all governing codes.
- The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- Using appropriate industry standard hardware as noted above.

**SAFETY INSTRUCTIONS:**  
All governing codes and regulations and those required by the job site must be observed.  
Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.



nVent, nVent CADDY, nVent ERICO, nVent GARDNER BENDER, nVent ILSICO, nVent KING INNOVATION, and nVent LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

## Vertical Mounting Strut or 1 1/4" Sch 40 Steel Pipe


1) When Cutting Strut: Open Side can Spring Open



2) Tap Open Side with Hammer / Mallet Back to Square (Fit Square Cut Out on PEKPSM)



Open Side of Strut




Lip Bottoms Out On Strut

1) Tighten Min 5 ftlbs [6.8Nm]

2) Tighten Jam Nut

Strut or 1 1/4" Sch 40 Pipe

CADDY PYRAMID Light Duty Equipment Support PEKLD4



PEKPSM

Can Prefab PEKPSM Complete (Power Switch Box, Wires, Conduit, etc.) Before Install on Site