



Description: Glazed door with fitted clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking program. Compatible with combinable and compact enclosure ranges.

Material: Frame: 2 mm steel plate. Viewing area: 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55 | TYPE 12 | IK 07.

Pack quantity: 1 piece.

Mounting requirements: Use hinge kit DNMK01 if no door was fitted previously.

H	W	VA h	VA w	Item no.
1400	600	1176	415	DNG1406R5
1400	800	1176	615	DNG1408R5
1600	600	1376	415	DNG1606R5
1600	800	1376	615	DNG1608R5
1800	600	1576	415	DNG1806R5
1800	800	1576	615	DNG1808R5
2000	600	1776	415	DNG2006R5
2000	800	1776	615	DNG2008R5
2000	1000	1776	815	DNG2010R5
2200	600	1976	415	DNG2206R5
2200	800	1976	615	DNG2208R5