

DP-PD

Partial doors | Répartition de puissance



Description: To divide the enclosure front into sections. Equipped with DIN 3 mm lock (1 lock up to 400 mm, 2 locks over 400 mm height).

Matériau: 1.75 mm mild steel.

Finition: RAL 7035 structured powder coating.

Protection: IP 44.

Unité de livraison: 1 door with hinges, locks and mounting accessories.

Instructions de montage: Add CDH for MC frames and use CDHK for MK frames.

H	L	Référence
150	600	DP01506R5
150	800	DP01508R5
200	600	DP02006R5
200	800	DP02008R5
250	600	DP02506R5
250	800	DP02508R5
300	600	DP03006R5
300	800	DP03008R5
400	600	DP04006R5
400	800	DP04008R5
500	600	DP05006R5
500	800	DP05008R5
600	600	DP06006R5
600	800	DP06008R5
800	600	DP08006R5
800	800	DP08008R5
1000	600	DP10006R5
1000	800	DP10008R5

** Available for MKSL and MCSL enclosures.*