

Fence Clamp, Three Conductor



The nVent ERICO Fence Clamp, Three Conductor, is designed to provide a reliable and efficient grounding solution for various applications. Manufactured from copper alloy, this clamp ensures maximum conductivity and durability. It features a multi-functional body design that allows for clamping parallel cables or wires to a pipe or rod in a perpendicular orientation and clamping three equal-sized cables to a metal pipe, rod, or post. Furnished with silicon bronze or stainless steel U-bolt, nut, and lock washer, this clamp is suitable for direct burial in earth or concrete, making it a versatile and dependable choice for grounding and bonding applications.

FEATURES

- Theft-deterrent appearance
- Silicon bronze or stainless steel hardware included
- Copper alloy minimizes the risk of corrosion
- Multi-functional body design

Finish: Bare
Material: Bronze

Part Number	Fence Post Size, Nominal	Conductor Size	Complies With
GR-4	0.375"	#4 Stranded - #8 Stranded	UL® 467
GR-5	0.375"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-6	0.375"	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-7	0.375"	500 kcmil - 300 kcmil	–
GR-9	0.5", 0.75"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-10	0.5", 0.75"	250 kcmil Stranded - 2/0 Stranded, 2/0 Stranded	UL® 467
GR-11	0.5", 0.75"	500 kcmil - 300 kcmil	–
GR-14	1"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-15	1"	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-16	1"	500 kcmil - 300 kcmil	–
GR-20	1.25"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-21	1.25"	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-26	1.5"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-27	1.5"	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-31	2"	#4 Stranded - #8 Stranded	UL® 467
GR-32	2"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-33	2"	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-38	2.5"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-39	2.5"	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-44	3"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-45	3"	250 kcmil Stranded - 2/0 Stranded	UL® 467
GR-50	3.5"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-61	4"	2/0 Stranded - 4/0 Stranded	UL® 467
GR-62	4"	250 kcmil Stranded - 2/0 Stranded	UL® 467

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE