

MPP-PD

Partial height mounting plates | Répartition de puissance



Description: Mounted directly on the enclosure's frame or onto the click-in profiles (CLPK). Special design of the bracket allows one man mounting. Can be mounted in any height or depth position within the 25 mm hole pattern. Appropriate sizes can also be used on the sides of the enclosure.

Matériau: 3 mm galvanized steel.

Unité de livraison: 1 plate with mounting accessories.

Instructions de montage: Add CLPK for depth adjustment.

Note: MPP can be mounted in both directions.

H/L	L/H	h/l	l/h	Référence
600	400	494	294	MPP0604
600	600	494	494	MPP0606
600	800	494	694	MPP0608
600	1000	494	894	MPP0610
800	400	694	294	MPP0804
800	800	694	694	MPP0808
1000	400	894	294	MPP1004
1000	800	894	694	MPP1008
1200	400	1094	294	MPP1204
1200	600	1094	494	MPP1206