


DOOR SWITCH, DSW, 52X40X63MM, PLASTIC

CATALOG NUMBER

DSW01



The door switch will allow lights or other electrical devices to turn on, or off, when the enclosure door is opened without the need for any manual interference.

INDUSTRY STANDARDS

CE
cCSAus
CCC

FEATURES

Approvals: CE, cCSAus.

Switch capacity: 3 A / 240 V.

Pack quantity: 1 piece with mounting accessories.

Description: Door switch to activate any electrical device (lighting, signalling, alarms, etc.). Can be mounted after installing the enclosure thereby keeping the door opening free. Fixed on the inside hole pattern of the enclosure's frame in floor standing enclosures. Cable entry M20.

PRODUCT ATTRIBUTES

Height: 52 mm

Width: 40 mm

Depth: 63 mm

Nominal Voltage: 240 V

Max Current: 3 A

Enclosure Material: Mild Steel; Stainless Steel

Product Family: Free-Standing

Material: Plastic

Finish: Smooth Matte

Color: Black Gray

Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER