

PROLINE INTERNAL COMPONENTS PRODUCT OVERVIEW



PROLINE Mounting Flexibility

We designed PROLINE internal components to provide an extensive range of mounting options. Whether your application calls for rack mounting, panel mounting or grid system mounting, a combination of PROLINE components can deliver the right solution. Plus, PROLINE internal mounting systems use standard fasteners for simple installation.

Panel Mounting

PROLINE's complete range of panel mounting options makes optimum use of internal enclosure space.

- A wider door opening offers more usable space for component mounting. Subpanels can be mounted front-to-back in 25-mm increments.
- Subpanels installed in the rear of joined enclosures provide a flush surface for component mounting
- Side-mount panels, partial-height panels and swing-out panels offer additional flexibility

Rack Mounting

If your application calls for 19-in., 23-in. or 24-in. mounted devices, PROLINE has a solution.

- 19-in., 23-in. and 24-in. rack-mount accessories include shelves, drawers and panels
- Adapter brackets allow rack angles to be used in wider cabinets
- Plated rack angles offer excellent conductivity for EMC-shielded applications

Grid System Mounting

A variety of grid mounting options lets you mount components directly on the PROLINE frame. Vertical and horizontal grid straps extend the internal framework while standard fasteners simplify installation and allow multi-source access to fasteners.

