

EF300-24R5

High flow filter fan



This vertical filter fan, EF, with a IP 54 protection degree, is easy to install thanks to its click-in feature. Unnecessary downtime is avoided, since water and dust are prevented from entering the enclosure through the filter, and the reliable fan motor will ensure constant ventilation.



IP 54 | TYPE 12

24 V DC

Bearing type	Ball
Connection	Spring type
Current (A)	0.50
Noise (dB)	42
EF+EFA Air flow (m³/h)	201/223
Connection Type	3
Unimpeded air-flow (m³/h)	223/247
Filter mat (EN779)	G4
Filtration efficiency (%)	>90
Service life L10 (40°C)(h)	80.000
Cut-out (mm)	223 × 223
Weight (kg)	1.45
Power (W)	12.00
Fuse (A)	6
Item no.	EF300-24R5

Description: Filter fan for forced ventilation. nVent HOFFMAN filter fans save time on installation as they are installed with a click-in system without screws. The hinged front cover can be easily opened for quick and easy filter replacement. The airflow direction and the connection position can easily be changed.

Material: Front cover manufactured from injection-moulded thermoplastic, self-extinguishing, UL94V0.

Temperature range: -40 °C to +55 °C.

Protection: IP 54 | TYPE 12.

Finish: RAL 7035.

Pack quantity: One fan with filter.