



Conduit Trapeze CCT4



The nVent CADDY Conduit Trapeze CCT4 range is a fast and cost-effective method to install larger feeder circuits of conduit in overhead trapeze installations. The CCT4 series reduces installation time and material cost by eliminating the need for traditional fasteners, making it an ideal solution for contractors looking to maximize installation efficiency.

FEATURES:

- Ideal for larger feeder circuits
- Accommodates ½ in threaded rod trapeze drops
- Up to 25% material savings over traditional methods
- Reduces installation time up to 50%
- Complies with UL® 2239

Material: Steel | Finish: Pregalvanized
EMT Conduit Size: 4" | Rigid Conduit Size: 4"



Part Number	Number of Conduits	Thickness T	Hole Size 1 HS1	Hole Size 2 HS2	Hole Size 3 HS3	Hole Size 4 HS4	Length 1 L1	Length 2 L2	Length 3 L3	Length 4 L4
CCT4X12	2	14 GA	9/16"	9/32"	1/8"	4 5/8"	12"	14"	6"	6"
CCT4X24	4	14 GA	9/16"	9/32"	1/8"	4 5/8"	24"	26"	6"	6"
CCT4X36	6	14 GA	9/16"	9/32"	1/8"	4 5/8"	36"	38"	6"	6"
CCT4X96	16	14 GA	9/16"	9/32"	1/8"	4 5/8"	96"	98"	6"	6"

UL Load Rating									
Orientation	Mounting Fastener	Fastener Spacing							
		6"	12"	18"	24"	30"	36"	42"	48"
Horizontal	½" Threaded Rod	600 lb	600 lb	550 lb	500 lb	475 lb	450 lb	425 lb	400 lb
Vertical	½" Fastener	600 lb	600 lb	—	—	—	—	—	—
Evenly Distributed Load Rating									
Horizontal	½"	—	650 lb	600 lb	550 lb	525 lb	500 lb	475 lb	450 lb

The table contains maximum conduit size values.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

