

# MCPL-IEC\_NA

Baying Bracket, MCPL



Type 12 | IP55



**Description:** Fixation baying brackets provide a rigid reinforcement of the assembly of MCS and MCD enclosures with a Proline enclosures. The correct spacing between the enclosures is assured as well as the IP rating of the bayed configuration.

**Feature:** A baying kit including snap-lines, mounted on the interior of the profiles, to allow for side-to-side baying of an IEC Modular Enclosure with a Proline floor standing enclosure.

**Advantage:** Tool free assembly without the need to remove the door and rear panel.

**Benefit:** Reduction of assembly time.

**Comment:** These brackets should not be used in combination with a separation plate or mounting plate if mounted on the side of the enclosure.

**Material:** Mild Steel

**Finish:**

- Baying Bracket - Zinc Plated
- Frame Extension Profile - Powder Coated Light Gray RAL7035

**Protection:** Complies with IP55 | NEMA TYPE 12

**Packaging Quantity:** 2 Brackets

For Type 3R MCS Enclosures

Item Number	HxWxD (mm/in.)	Fits Enclosure
MCPL400	46x101x400 1.8x3.98x15.74	400mm Deep (15.74)
MCPL500	46x101x500 1.8x3.98x19.68	500mm Deep (19.68)
MCPL600	46x101x600 1.8x3.98x23.62	600mm Deep (23.62)
MCPL800	46x101x800 1.8x3.98x31.45	800 Deep (31.45)