

Förbättrad nVent-CADDY Cat HP J-krok Mod Clip med stång/trådklämma



Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

CERTIFIERINGAR



DESIGN

verktygsfri montering

Works with nVent J-Hook Versa-Mount technology from nVent CADDY

SPECIFIKATIONER

Table 1/1						
Katalognummer	Artikelnummer	Slutför	Material	Stångstorlek (RS)	Kabelstorlek	Statisk belastning
CATHPM4Z34	186082	nVent CADDY rustning	Fjäderstål	M4, M6, M8, M10, M12	4.8 - 6.4 mm	130N



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vårt starka utbud av varumärken:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

